

**BOSCH**

Invented for life

Power tools for trade &amp; industry

## Product data sheet



Jigsaw

### GST 150 CE

The most powerful tool in its price class

#### The most important data

Rated power input	780 W
Cutting depth in wood	150 mm
Cutting depth in aluminium	20 mm

**Part number:** 0 601 512 070**GBP 145,00\***[> More product information](#)*\* Recommended retail price excluding VAT*

#### Technical data

Rated power input	780 W
Stroke rate at no load	500 – 3.100 spm
Weight	2,6 kg
Cable length	4 m
Stroke height	26 mm
Cutting depth	
Cutting depth in wood	150 mm
Cutting depth in aluminium	20 mm
Cutting depth in unalloyed steel	10 mm

#### Noise/vibration information

Sawing sheet metal	
Vibration emission value ah	7.0 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>
Sawing wood	
Vibration emission value ah	8.0 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

**Power tools for trade & industry****Advantages:**

- High power reserves, even in hard and thick beams, due to powerful and overload-capable 780-watt motor
- Extremely robust and bend-resistant sole plate for the toughest jobs
- High cutting precision due to new saw blade clamping system
- Tool-free saw blade clamping system for easy and fast saw blade changes
- Ergonomic grip area with softgrip surfaces for a high level of comfort during use
- 4-stage pendulum action for fine through to coarse cuts

**Prices / Scope of delivery**

Part number	0 601 512 070
1 x saw blade T 144 DP (ET no. 2 609 991 569)	✓
Anti-splinter guard 2 601 016 096	✓
Dust extraction set 2 605 510 294	✓
Glide shoe (ET no. 2 601 099 183)	✓
Hood (ET no. 2 605 510 293)	✓
Suction nozzle (ET no. 2 605 730 055)	✓
Voltage 240 V	✓
<b>Price</b> (Recommended retail price excluding VAT)	<b>GBP 145,00</b>