



ENGLISH

Datasheet

Stock No: 199-652

RS Pro 1.2V NiMH Tagged Terminal 1/2 AA NiMH Rechargeable Battery



Product Details

RS Pro, Standard Tagged

Tagged to allow for combining into larger battery packs for permanent installation

Voltage 1.2V

Quick 4 to 6hr charging rate.

Note

All batteries are supplied with only a residual charge and should be charged at the continuous charge rate before use.

Caution

Do not connect batteries in parallel.

NiMH Rechargeable Industrial Batteries

Improved performance over NiCd batteries.



Specifications

Size	1/2 AA
Nominal Voltage	1.2V
Capacity	550mAh
Chemistry	NiMH
Dimensions	23.9 x 14.3mm
Terminal Type	Tagged
Maximum Continuous Current	3mA
Operating Temperature Range	-10 → +60°C
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C