



ENGLISH

## Datasheet

Stock No: 235-663

# RS Pro Incandescent Beacon, Flashing, Surface Mount, 230 V ac



## Product Details

### Flashing Filament Beacons

Weatherproof and dustproof to IP56 these beacons offer high quality solutions for industrial environments and process applications.

- Approximately 80 flash per minute
- 60W light output where bulb is supplied
- High protection rating of IP56
- Optional cage guard for three point mount versions
- Surge protection for safety against peak voltage
- Full internal suppression for maximum interference reduction
- 166mm diameter
- Three point mounting



ENGLISH

**Note**

Lens must be purchased separately

**Supplied with**

Bulb (except 12/24V versions)

## Specifications:

Supply Voltage	230 V ac
Light Effect	Flashing
Lens Colour	Lens Not Included
Mounting Style	Surface Mount
Bulb Type	Incandescent
Current Type	AC
Base Diameter	166mm
Housing Colour	Black
Lamp Included	Yes
Series	V10993
Height	207mm
Minimum Temperature	-30°C
Maximum Temperature	+50°C