



ENGLISH

Datasheet

Stock No: 243-513

# RS Pro 7 Piece Precision Screwdriver Set



## Product Details

Precision Driver Sets

RS Precision screwdrivers ideally suited for the electronic industry.

Blades made from high grade Chrome-vanadium steel

Rotating cap allows user to drive easily and adjust precisely

Tri-lobe shape of handle provides comfortable gripe during rotation



ENGLISH

## Product Details

Selection Guide			
Pieces	Style	Size	Stock No
7	Slotted (4) Philips (3)	1.5x50, 2.5x50, 3x5, 3x100 00x60, 0x60, 1x80	243-513
7	Slotted (4) Philips (3)	2.5x50, 2.5x50, 3x50, 3x100 00x60, 0x60, 1x80	243-585
5	Torx	T6X60, T7x60, T8x60, T9x60, T10x100	243-692
7	Hex	0.6x60, 0.7x60, 1.3x60, 1.5x60, 2.0x60, 2.5x100, 3.0x100	243-686
5	Nut Spinner	2.5, 3, 3.2, 3.5, 4 x 60 mm	243-664

Parts	Model		Stock no.
7 to	Hex.	0.6 x 60, 0.7 x 60, 1.3 x 60, 1.5 x 60, 2.0 x 60, 2.5 x 100, 3.0 x 100	243-686
5	Nut driver	2.5, 3, 3.2, 3.5, 4 x 60 mm	243-664
5	TORX®:	T6 x 60, T7 x 60, T8 x 60, T9 x 60, T10 x 100	243 to 692
7 to	Slotted/Phillips	Slotted: 1.5 x 50, 2.5 x 50, 3 x 5, 3 x 100 ; Ph00 x 60, Ph0 x 60, Ph1 x 80	243-513

### Note

Packaged in a cardboard box. For a suitable wallet see stock no 647-053

### Miniature & Precision Sets



ENGLISH

## Specifications:

Screwdriver Type	Precision
Number of Pieces	7
Tip Type	Slotted; Phillips
Tip Size	Slotted: 1.5; 2.5; 3; 3 mm; Phillips: PH00; PH0; PH1
Set Contents	Pozidriv:PZ1 x 100, PZ2 x 125 mm
Blade Length	Slotted: 50; 50; 50; 100; Phillips: 60; 60; 80 mm
Blade Material	Chrome Steel