



ENGLISH

Datasheet

Stock No: 541-860

# RS Pro 6mm Lever Press Circular Punch & Die Combinations



## Product Details

### Circular Hole Punches and Dies Tool Steel

Fully hardened and tempered tool steel punches and dies for accurate, clean hole punching in a wide range of materials. Dies are counterbored to prevent material build up. For accurate hole alignment, smaller punches (3 to 12 mm) include a fixed centre location point. Larger punches (12.5 to 25 mm) have a retractable spring loaded centering pin. See table below for max. material thicknesses

Punch & Die Set	Maximum Thickness			
	3000lb Press		5000lb Press	
	Steel	Aluminium	Steel	Aluminium
3 to 5mm	1.6	2.5	1.6	2.5
6 to 10mm	1.6	2.5	2	3

## Specifications:

Hole Shape	Circular
Operation	Lever Press
Hole Size	6mm
Cutting Capacity	Steel: 2 mm; Aluminium: 3 mm