



ENGLISH

Datasheet

Stock No: 797-388

RS Pro PVC transparent Flexible Tube 25m Long , 225mm Bend Radius



Product Details

Clear Non-reinforced PVC Hose

- Outstanding resistance to ageing
- Low toxicity, suitable for food use and technical applications
- Resistance to a wide range of chemicals with high resistance to acids/alkalis
- Safety factor 3:1

Note

- Working Pressure is at 23°C

PVC Industrial Hoses - Clear

A range of industrial hoses made from Cadmium free materials. Offering excellent abrasion resistance and good flexibility, they are Silicone free with a service temperature of -15°C to +60°C.



ENGLISH

Specifications:

Inner Diameter	19mm
Outer Diameter	25mm
Material	PVC
Colour	Transparent
Suitable Applications	Alcohol, Grease, Oil, Petrol, Solvent
Length	25m
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	4 bar
Bend Radius	225mm
Operating Temperature Range	-15 to +60 °C