



ENGLISH

Datasheet

Stock No: 193-8029

RS Pro Straight 50Ω Cable Mount TNC Connector, jack, Crimp Termination, RG58 C/U



Product Details

Nickel Plated

Brass bodied TNC connectors with PTFE insulators and gold plated contacts.

Bulk kit containing 100 RG58 straight plugs [546-5200](#) is available, making production and servicing much easier. Component parts are neatly stored in a sturdy dispensing case

Body Material	Nickel plated brass
Contact Material	Gold plated copper alloy
Insulator Material	PTFE
Working Voltage	500V peak
Proof Voltage	1500V peak
Temperature Range	-40°C to +155°C

Nominal Impedance	50Ω and 75Ω
Operating Voltage	500V rms at sea level
Contact Resistance	Outer : 0.2mΩ Centre : 1.5mΩ
Insulation Resistance	5000mΩ
Dielectric	PTFE
Centre Contact	Gold plated



ENGLISH

Specifications:

Gender	Female
Body Orientation	Straight
Termination Method	Crimp
Mounting Type	Cable Mount
Body Plating	Nickel
Cable Type	RG58 C/U
Impedance	50Ω
Operating Frequency	0 → 11GHz
Contact Plating	Gold over Nickel over Copper
Contact Material	Beryllium Copper