



ENGLISH

Datasheet

Stock No: 278-9086

RS Pro Hydraulic Pressure Gauge Isolation Valve, G 1/4 Female



Product Details

Angled Gauge Isolator Needle Valves

Protect pressure gauge by dampening shock of pressure during opening and isolating pressure line
All valves have swivel adaptor to allow gauge-to-face position required

Gauge Isolation Valves



Specifications

Orientation	Angled
Connection Port Thread	G 1/4 Female
Body Material	Carbon Steel
Maximum Operating Pressure	400 bar
Minimum Operating Temperature	-20°C
Thread Diameter	1/4 in
Thread Gender	Female
Thread Standard	G
Maximum Operating Temperature	+100°C