
P RF CLAS ST 25 2 W/827 E27

PARATHOM Retrofit CLASSIC ST | LED lamps, classic Edison bulb shape



Areas of application

- Domestic applications
- General illumination
- Outdoor applications only in suitable luminaires
- Perfect for decorative installations

Product benefits

- Clear lamps with innovative LED "filament" technology
- Very low energy consumption
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs

Product features

- Professional LED lamps for line voltage
- Not dimmable
- Mercury-free lamps
- Lifetime: up to 15,000 h
- Beam angle: up to 360°
- Energy efficiency class: A++



Product datasheet

Technical data

Electrical data

Rated wattage	2.00 W
Nominal wattage	2.00 W
Nominal voltage	220...240 V
Operating frequency	50...60 Hz
Power factor λ	> 0.40
Claimed equiv. conventional lamp power	25 W


Photometrical data

Nominal luminous flux	250 lm
Rated luminous flux	250 lm
Color temperature	2700 K
Color rendering index Ra	≥ 80
Light color (designation)	Warm White
Standard deviation of color matching	≤ 6 sdc _m

Light technical data

Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & weight



Overall length	143.0 mm
Diameter	64.0 mm
Outer bulb	ST64
Length	143.0 mm

Lifespan

Product datasheet

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen main.fact.at end of nom.life time	0.70
Lumen maintenance at end of service life	0.70

Additional product data

Base (standard designation)	E27
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Clear
Appropriate disposal acc. to WEEE	Yes

Capabilities

Dimmable	No
----------	----

Certificates & standards

Energy efficiency class	A++
Energy consumption	2 kWh/1000h

Country specific categorizations

ILCOS	DRAS/C-2/827-220/240-E27-64
Order reference	PRFCLST64252W/8

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899962125	P RF CLAS ST 25 2 W/827 E27	Shipping carton box 10	337 mm x 141 mm x 161 mm	7.65 dm ³	735.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.