



Datasheet

Stock No: 310-8977

ENGLISH

RS Pro 10A 1 Gang Switched Surface Mount Fused Connection Unit IP67



Product Details:

Fused Spur - Weatherproof

- Enclosure provides protection to IP67
- Does not need resetting after power failure
- RCD status indication
- Conforms to BS5733, BS7288, BSEN60529

Power Breaker RCDs

- Providing protection against electrocution
- Double pole switching on all types
- Trip Current 30mA
- Twin earth terminal
- All terminals are in-line with captive screws for ease of installation
- Detects pulsating dc fault currents to protect electronic equipment, loss of earth and neutral and reversed supply polarity
- 230Vac 50Hz
- Suitable for Flush or surface mounting
- Single and double gang sockets fit in place of standard sockets
- Integral set and indicator button
- Resistant to nuisance tripping
- Typical trip speed <40ms



Specifications:

Number of Gangs:	1
Switched:	Yes
Current Rating:	10A
Trip Speed:	20ms
Trip Current:	30mA
Minimum Box Depth:	76mm
Mounting Style:	Surface Mount
RCD Type:	Passive
Fuse Type:	BS 1363-4, BS 7288
International Protection Rating:	IP67
Number of Poles:	2
Length:	125mm
Depth:	76mm
Width:	125mm
Voltage Rating:	230 V ac
Dimensions L x W x D:	125 x 125 x 76mm
Earth Terminal:	Yes