



ENGLISH

Datasheet

Stock No: 123-7932

RS Pro Candle 5.6W (40W) 2700k 470lm E14 Dimmable Frosted Lamp



Specifications:

Lamp Base: E14

Lamp Shape: Candle

Wattage: 5.6W

Voltage Rating: 220-240V

Length: 102mm

Diameter: 35mm

Current Rating: 58mA

Frequency Range: 50Hz

Electric Current: AC

Features:

The Base Colour is Matt white Candle frosted finish. Material is Plastic with polycarbonate and Nickel plated brass with the lamp fixing pendant, chandelier or wall.



ENGLISH

Heat Graph: Warm

2700 K

