

# Sales Presenter

## DVD+R AZO Wide Inkjet Printable – No ID Brand

**Reorder No:** 43512

**Warranty:** Lifetime (2yrs Germany)

### Features:

- Capacity: 4.7GB
- Speed: 16x
- Pack Style: 50 Pack Spindle
- Disc Surface: Wide Inkjet Printable – No ID Brand
- Print area: 21 – 118mm
- AZO recording layer for optimum recording quality.

**Barcode:** 023942435129  
**EAN 128:** (02)00023942435129(37)0200(91)04  
**EAN 14:** 50023942435124  
**Carton Qty:** 200  
**Carton Dimensions:** 590mm x 120mm x 150mm  
**Pack Weight:** 470g  
**Pack Dimensions:** 142x142x91mm  
**Layers Per Pallet:** 4 layers  
**Cartons / layer:** 20pcs  
**Units / Pallet:** 16000pcs

