



D28710

355 mm Abrasive Chop Saw

Features and Benefits

- Horizontal handle for superior ergonomics and less user fatigue
- Quick release clamp results in less time in changing the work piece
- High power abrasion protected motor delivers high overload capabilities for greater durability
- Spindle lock for quick and easy wheel change
- Adjustable spark guard allows user to control the direction of the sparks coming from the machine

Specifications	
Power Input	2200 Watts
Power Output	1350 Watt
No Load Speed	3800 rpm
Wheel Diameter	355 mm
Max. Cutting Capacity at 90° [Square Profile]	120 x 120 mm
Max. Cutting Capacity at 90° [Rounded Profile]	130 mm
Max. Cutting Capacity at 45° [Square Profile]	107 x 107 mm
Max. Cutting Capacity at 45° [Rounded Profile]	115 mm