

# Comus Europe Reed Switch Kit Selection Guide



Comus Part No	New RS Description	RS Code Number	Description	AT Rating
RI-03AAA	RI-03H	9092572	14.5mm Glass Reed Switch / 200V /Form A	6-16
RI-03AA	RI-03M	9092581	14.5mm Glass Reed Switch / 200V /Form A	14-23
RI-03A	RI-03L	9092584	14.5mm Glass Reed Switch / 200V /Form A	18-32
<b>RI-03 Kit</b>	<b>RI-03K</b>	<b>9092588</b>	<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>6-16 / 14-23 / 18-32</b>
RI-07AAA	RI-07H		13.5mm Glass Reed Switch / 200V /Form A	5-10
RI-07AA	RI-07M	3622502	13.5mm Glass Reed Switch / 200V /Form A	16-25
<b>RI-07 Kit</b>	<b>RI-07K</b>		<b>Qty 1 of each High/Med Sensitivity</b>	<b>5-10 / 16-25</b>
RI-23A	RI-23H	9092604	14.5mm Glass Reed Switch / 200V /Form A	18-32
RI-23B	RI-23M	9092607	14.5mm Glass Reed Switch / 200V /Form A	28-52
RI-23C	RI-23L	9092601	14.5mm Glass Reed Switch / 200V /Form A	46-70
<b>RI-23 Kit</b>	<b>RI-23K</b>	<b>9092610</b>	<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>18-32 / 28-52 / 46-70</b>
RI-26AA	RI-26H	9092613	14.5mm Glass Reed Switch / Close Differential / 200V /Form A	14-23
RI-26A	RI-26M	9092617	14.5mm Glass Reed Switch / Close Differential / 200V /Form A	18-32
RI-26B	RI-26L	9092626	14.5mm Glass Reed Switch / Close Differential / 200V /Form A	28-52
<b>RI-26 Kit</b>	<b>RI-26K</b>		<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>14-23 / 18-32 / 28-52</b>
RI-27AAA	RI-27H	9092623	13.5mm Glass Reed Switch / 180V /Form A	10-20
RI-27AA	RI-27M	9092632	13.5mm Glass Reed Switch / 180V /Form A	15-25
RI-27A	RI-27L	9092635	13.5mm Glass Reed Switch / 180V /Form A	20-34
<b>RI-27 Kit</b>	<b>RI-27K</b>	<b>9092639</b>	<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>10-20 / 15-25 / 20-34</b>
RI-46A	RI-46H	9092648	20.5mm Glass Reed Switch / 200V /Form A	15-28
RI-46B	RI-46M	9092641	20.5mm Glass Reed Switch / 200V /Form A	24-51
RI-46C	RI-46L	9092645	20.5mm Glass Reed Switch / 200V /Form A	46-70
<b>RI-46 Kit</b>	<b>RI-46K</b>	<b>9092654</b>	<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>15-28 / 24-51 / 46-70</b>
RI-60	RI-60H	9092657	10.0mm Glass Reed Switch / 200V /Form A	10-15
RI-60B	RI-60M	9092651	10.0mm Glass Reed Switch / 200V /Form A	15-20
<b>RI-60 Kit</b>	<b>RI-60 K</b>	<b>9092660</b>	<b>Qty 1 of each High/Med Sensitivity</b>	<b>10-15 / 15-20</b>
RI-70	RI-70H	9092663	7.0mm Glass Reed Switch / 170V /Form A	5-10
RI-70B	RI-70M	9092667	7.0mm Glass Reed Switch / 170V /Form A	10-15
RI-70C	RI-70L	9092676	7.0mm Glass Reed Switch / 170V /Form A	15-20
<b>RI-70 Kit</b>	<b>RI-70K</b>	<b>9092679</b>	<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>5-10 / 10-15 / 15-20</b>
RI-80	RI-80H	9092673	5.0mm Glass Reed Switch / 175V /Form A	5-10
RI-80B	RI-80M	9092682	5.0mm Glass Reed Switch / 175V /Form A	10-15
<b>RI-80 Kit</b>	<b>RI-80K</b>	<b>9092685</b>	<b>Qty 1 of each High/Med Sensitivity</b>	<b>5-10 &amp; 10-15</b>
RI-90	RI-90H	9092689	14.3mm Glass Reed Switch / 175V /Form C	10-15
RI-90B	RI-90M	9092698	14.3mm Glass Reed Switch / 175V /Form C	20-25
RI-90C	RI-90L		14.3mm Glass Reed Switch / 175V /Form C	30-35
<b>RI-90 Kit</b>	<b>RI-90K</b>	<b>9092695</b>	<b>Qty 1 of each High/Med/Low Sensitivity</b>	<b>10-15 / 20-25 / 30-35</b>

Comus Part No	New RS Description	RS Code Number	Description	AT Rating
GC2522 (10-20AT)	GC2522H	9092705	11.0mm Glass Reed Switch / 140V / Form A	10-20
GC2522 (20-30AT)	GC2522M	9092708	11.0mm Glass Reed Switch / 140V / Form A	20-30
GC2522 (30-40AT)	GC2522L	9092702	11.0mm Glass Reed Switch / 140V / Form A	30-40
	GC2522K	9092711	Qty 1 of each High/Med/Low Sensitivity	10-20 / 20-30 / 30-40
GC2322 (10-15AT)	GC2322H	9092714	14.0mm Glass Reed Switch / 150V / Form A	10-15
GC2322 (15-25AT)	GC2322M	9092718	14.0mm Glass Reed Switch / 150V / Form A	15-25
GC2322 (25-35AT)	GC2322L	9092727	14.0mm Glass Reed Switch / 150V / Form A	25-35
	GC2322K	9092720	Qty 1 of each High/Med/Low Sensitivity	10-15 / 15-25 / 25-35
GC2314 (10-15AT)	GC2314H	9092724	14.0mm Glass Reed Switch / 400V / Form A	10-15
GC2314 (15-25AT)	GC2314M	9092733	14.0mm Glass Reed Switch / 400V / Form A	15-25
GC2314 (25-35AT)	GC2314L	9092736	14.0mm Glass Reed Switch / 400V / Form A	25-35
	GC2314K	9092730	Qty 1 of each High/Med/Low Sensitivity	10-15 / 15-25 / 25-35
GC2722 (20-30AT)	GC2722H	9092749	19.0mm Glass Reed Switch / 230V / Form A	20-30
GC2722 (30-40AT)	GC2722M	9092742	19.0mm Glass Reed Switch / 230V / Form A	30-40
GC2722 (40-50AT)	GC2722L	9092746	19.0mm Glass Reed Switch / 230V / Form A	40-50
	GC2722K	9092755	Qty 1 of each High/Med/Low Sensitivity	20-30 / 30-40 / 40-50
GC3723 (15-25AT)	GC3723H	9092758	19.0mm Glass Reed Switch / 230V / Form A	15-25
GC3723 (25-35AT)	GC3723M	9092752	19.0mm Glass Reed Switch / 230V / Form A	25-35
GC3723 (35-50AT)	GC3723L	9092761	19.0mm Glass Reed Switch / 230V / Form A	35-50
	GC3723K	9092764	Qty 1 of each High/Med/Low Sensitivity	15-25 / 25-35 / 35-50
GC3717 (15-25AT)	GC3717H	9092768	19.0mm Glass Reed Switch / 400V / Form A	15-25
GC3717 (25-35AT)	GC3717M	9092777	19.0mm Glass Reed Switch / 400V / Form A	25-35
GC3717 (35-50AT)	GC3717L	9092770	19.0mm Glass Reed Switch / 400V / Form A	35-50
	GC3717K	9092774	Qty 1 of each High/Med/Low Sensitivity	15-25 / 25-35 / 35-40
GC3823 (30-40AT)	GC3823H	9092783	24.5mm Glass Reed Switch / 230V / Form A	30-40
GC3823 (45-60AT)	GC3823M	9092786	24.5mm Glass Reed Switch / 230V / Form A	45-60
GC3823 (60-70AT)	GC3823L	9092780	24.5mm Glass Reed Switch / 230V / Form A	60-70
	GC3823K	9092799	Qty 1 of each High/Med/Low Sensitivity	30-40 / 45-60 / 60-70
GC3817 (30-40AT)	GC3817H	9092792	24.5mm Glass Reed Switch / 400V / Form A	30-40
GC3817 (45-60AT)	GC3817M	9092796	24.5mm Glass Reed Switch / 400V / Form A	45-60
GC3817 (60-70AT)	GC3817L	9092806	24.5mm Glass Reed Switch / 400V / Form A	60-70
	GC3817K	9092809	Qty 1 of each High/Med/Low Sensitivity	30-40 / 45-60 / 60-70
GC1513 (60-70AT)	GC1513H	9092803	52.0mm Glass Reed Switch / 1500V / Form A	60-70
GC1513 (70-80AT)	GC1513M	9092812	52.0mm Glass Reed Switch / 1500V / Form A	70-80
GC1513 (80-95AT)	GC1513L	9092815	52.0mm Glass Reed Switch / 1500V / Form A	80-95
	GC1513K	9092819	Qty 1 of each High/Med/Low Sensitivity	60-70 / 70-80 / 80-95
GC1917 (40-60AT)	GC1917H	9092828	36.0mm Glass Reed Switch / 400V / Form C	40-60
GC1917 (60-80AT)	GC1917M	9092821	36.0mm Glass Reed Switch / 400V / Form C	60-80
GC1917 (80-100AT)	GC1917L	9092825	36.0mm Glass Reed Switch / 400V / Form C	80-100
	GC1917K	9092834	Qty 1 of each High/Med/Low Sensitivity	40-60 / 60-80 / 80-100
GC1625 (80-90AT)	GC1625H	9092837	52.0mm Glass Reed Switch / 230V / Form C	80-90
GC1625 (90-105AT)	GC1625M	9092831	52.0mm Glass Reed Switch / 230V / Form C	90-105
GC1625 (105-120AT)	GC1625L	9092840	52.0mm Glass Reed Switch / 230V / Form C	105-120
	GC1625K	9092843	Qty 1 of each High/Med/Low Sensitivity	80-90 / 90-105 / 105-120