

---

## SPOT LED 8 W 4000 K IP44 DIM SL

LEDVANCE SPOT LED | LED spotlight luminaires



---

### Areas of application

- Replacement of conventional 50 W halogen spotlights
- General illumination
- Hotel rooms
- Bars, restaurants
- Accent lighting
- Galleries, museums

---

### Product benefits

- Design matches the LEDVANCE DOWNLIGHT luminaire family
- Energy savings of up to 90 % compared to halogen lamp spotlights
- Functional and minimalistic design
- Easy and quick installation
- External driver for extended flexibility (compatible with selected DALI drivers)
- 3 years guarantee

---

### Product features

- Luminous efficacy: 85 lm/W
- Luminous flux: up to 550 lm
- Color temperature: 3,000 K
- Initial color consistency:  $\leq 4$  SDCM
- Beam angle: 36°
- Compatible with standard ceiling cutouts of 68 mm
- Type of protection: IP20
- Housing material: aluminum



## Product datasheet

- Lens material: PMMA
- Lifetime: up to 30,000 h
- Certificates: CE, CB, TUEV SUED

## Technical data

### Electrical data

Operating mode	Electronic control gear (EVG)
Nominal wattage	8.00 W
Nominal voltage	220...240 V
Mains frequency	50/60 Hz

### Photometrical data

Color temperature	4000 K
Luminous flux	670 lm
Light color (designation)	Cool White
Color rendering index Ra	>80

### Light technical data

Beam angle	36 °
------------	------

### Dimensions & weight

Diameter	81.0 mm
Height	51.0 mm
Mounting diameter	68 mm

### Colors & materials

Body material	Aluminum
Product color	Silver

### Temperatures & operating conditions

Ambient temperature range	-20...45 °C
---------------------------	-------------

### Lifespan

Lifespan	30000 h
----------	---------

### Capabilities

Dimmable	Yes
Type of connection	Terminal, 2-pin

### Certificates & standards

Protection class	II
Type of protection	IP44

## Product datasheet

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075811317	SPOT LED 8 W 4000 K IP44 DIM SL	Shipping carton box 27	440 mm x 320 mm x 360 mm	50.69 dm <sup>3</sup>	10.08 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.