

Datasheet

RS Pro Clear Passivated, Zinc Steel Hex Bolt, M16 x 80mm

RS Stock No: **279-925**



Product Details

RS Pro hex bolt is of size M16 x 80 mm, features clear passivated, zinc steel construction for long life durability. Hex bolt is partially threaded and can be used with a nut or in a tapped hole. This bolt is tightened with a wrench. The hex bolt meets DIN 931 standards.

Features and Benefits

- Good corrosion resistance
- Recyclable
- Non-magnetic
- It is suitable for machine repairs and outdoor applications
- Threaded in accordance with DIN 931

**Specifications:**

Finish	Bright Zinc Plated, Clear Passivated
Material	Steel
Steel Type	High Tensile Steel
Grade	8.8
Length	80 mm
Thread Pitch	2
Thread Size	M16
Head Height	10 mm
Specification	DIN 931
Width Across Corners	26.75 mm
Width Across Flats	24 mm