

Datasheet

RS Pro Steel Alloy Compression Spring, 28mm x 4.8mm, 3.52N/mm

RS Stock No: **751-528**



Product Details

RS Pro stainless steel alloy compression spring measures 28 x 4.8 mm and has a spring rate of 3.52 N/mm. It handles a load of 31.87 N at a minimum working length of 19.1 mm. This spring features right hand helix construction.

Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



Specifications:

Ends	Closed (Square)/Unground
Material	Steel Alloy
Free Length	28 mm
Load at Minimum Working Length	31.87 N
Minimum Working Length	19.1 mm
Outside Diameter	4.8 mm
Spring Rate	3.52 N/mm
Wire Diameter	0.8 mm