



ENGLISH

Datasheet

10m Long 94 bar Copper Tubing, -50 → +200°C

RS Stock number 0846480



Features

Standard Duty, Annealed Copper Tube

Annealed, standard duty copper tube

Use with Enots compression fittings

Operating Temperature Range -50 → +200 °C

CW024A grade