

Datasheet

Croc Clip ESD Grounding Wrist Strap & Cord Set

RS Stock number [287-7385](#)



Description

- Premium quality fabric band and cord set with fully adjustable wrist strap fits all sizes
- Band constructed using premium crochet fabric band with elastic ratio of 1:2.5" to 1:3".
- Outer surface of band is non-conductive and inner surface of the strap is conductive, lined with 5-rows of double-ply silver yarn.
- The ground end of the cord possesses PU strain relief assembly with nylon encapsulated body housing. Moulded snap body is with tear-drop design.
- Cord construction - The body housing contains 10mm female snap, with or without resistor joined in series to the conductor with ribbed banana plug, crimped or moulded eyelet, or another snap on the other end.
- The cord conductor has an end to end resistance not greater than 1 ohms.



Specifications

- Band Material
- Cord Length
- Cord Style
- Includes Cord
- Lead Resistance
- Stud Size
- Termination Type
- Wrist Strap Size
- Interior Cuff Resistance
- Exterior cuff Resistance
- Fabric
- 1.8m
- Coiled
- Yes
- 1M Ω
- 10mm
- Press Stud
- Adjustable
- ≤ 100 Kiloohms at 7 to 30 volts dc Open Circuit
- ≥ 10 Megohms