



ENGLISH

Datasheet

RS Pro Brass Pneumatic Quick Connect Coupling, G 1/4 Male, Threaded

RS Stock No: **492-8665**



Product Details

RS Pro pneumatic quick connect coupling withstands pressure up to 35 bar. This brass coupling has nickel plated finishing for added durability. It offers connection through G 1/4 Inch male threaded end.

Features and Benefits

- Threaded connection
- Nickel plated brass
- Simple construction

**Specifications:**

Connection Standard	ISO B
Connection Type	Threaded
Coupling Gender	Male
Finish	Nickel Plated
Material	Brass
Seal Material	Perbunan
Thread Gender	Male
Thread Standard	G
Threaded Connection	G 1/4 Male
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Maximum Operating Pressure	35 bar
Thread Size	1/4 in
Length	52 mm