

Datasheet

RS Pro Stainless Steel Bolt Anchor M8, fixing hole diameter 8mm, length 50mm

RS Stock No: **622-1922**



Product Details

RS Pro captive stud bolt anchor made of A4-316 grade stainless steel resist corrosion. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm². The bolt anchor measures 50 mm long with M8 threading that is suitable for 8 mm fixing hole diameter.

Features and Benefits

- Captive stud through bolt anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm²
- 8 mm fixing hole diameter
- 50 mm long



Specifications:

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	8 mm
Length	50 mm
Maximum Fixing Thickness	5 mm
Thread Size	M8
Grade	316 (A4)
Minimum Hole Depth	45 mm