



Datasheet

ENGLISH

Brass Pneumatic Y Threaded-to-Tube Adapter, R 1/4 Male

RS Stock number 6671712



Features

Interchangeability: PCL 60 Standard Series, Rectus 19

Temp.Range: -20°C to +100°C

Working Pressure: 0-35 bar (0-500 PSI)

Flow Capacity: NW -5.5

Options:

K - Chrome plated

V - Viton Seal

Material

Coupler Body - Brass Nickel Plated

Back Part - Brass Nickel

Sleeve - Steel Nickel Plated

Valve - Brass

Springs - Stainless Steel

Locking O-Ring - Stainless Steel

Balls/Pins - Stainless Steel

Seals - Buna (M)

Plug - Steel Nickel Plated