

Datasheet

Moulded Momentary Foot Switch

RS Stock No. 116-681



Degree of protection	IP20
Materials of Construction	Corrosion proof reinforced polymeric.
Colour	Dark Grey.
Cable Connection	Adjustable strain relief clamp accommodates a wide range of cable sizes.
Contact Action	DPDT Momentary.
Electrical Rating	15A 125-250V a.c, 0.375kW 125-250V a.c.
Features & Benefits	Flame retardant. Raised ribs on operating cover ensures good grip. Non-skid base pads.
Weight	0.1kg
Size	(See below)

