

## Datasheet

# HSS 5mm Jobber Drill Bit Plain Shank

RS Stock number [213-203](#)



### Description:

HSS TiN Coated, High Speed Steel Titanium nitride coated drill bit.

### Product Details:

- Straight shank
- Right hand cutting
- DIN338; BS328-ISO235/1
- Standard : DIN338 right hand spiral
- Material : HSS M2
- Point Angle : 118°
- Surface : Tin-coated

**Dimension:**

RS Stock No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
213-887	1.0	34	12
213-900	1.1	36	14
213-310	1.2	38	16
213-893	1.3	38	16
213-376	1.4	40	18
213-871	1.5	40	18
213-859	1.6	43	20
213-433	1.7	43	20
213-865	1.8	46	22
213-972	1.9	46	22
213-916	2.0	49	24
213-966	2.1	49	24
213-950	2.2	53	27
213-944	2.3	53	27
213-938	2.4	57	30
213-922	2.5	57	30
213-843	2.6	57	30
213-764	2.7	61	33
213-758	2.8	61	33
213-427	2.9	61	33
213-411	3.0	61	33
213-382	3.1	65	36
213-405	3.2	65	36
213-398	3.3	65	36
213-742	3.4	70	39
213-304	3.5	70	39
213-720	3.6	70	39
213-714	3.7	70	39
213-736	3.8	75	43
213-837	3.9	75	43