



ENGLISH

Datasheet

32 – 152 mm bimetal Arbor

RS Stock number [215-978](#)



Description:

Hardened cutting edge (6tpi alternate set) welded to a tough alloy steel body
Bonded construction reduces possibility of shattering
For use with ferrous and non ferrous metals, plastics and wood to a depth of 32mm
14 to 30mm diameter saws require a 6.5mm arbour
32 to 152mm diameter saws require a 9.5mm arbour
Arbours, pilot drills and core removal tools available

Specifications:

Bimetal: Yes
Diameter: 9.5 mm
Supported Holesaw Size: 32 – 152 mm