



ENGLISH

## SPECIFICATION SHEET 358012

### SOFT TINNED COPPER WIRE BRAID 2531P

CONSTRUCTION : 16x6x0.15MM

RESISTANCE : 10.3 OHMS/KM STANDARD RESISTANCE @ 20 DEG C.

YIELD : 17.3KGS/1000M

TENSILE : N/A

WIRE : MANUFACTURED TO BS4109 C101.0

RoHS : COMPLIANT