



ENGLISH

Datasheet

RS Pro 150 mm Chrome Vanadium Steel Combination Pliers, Jaw Length: 34mm

RS Stock No: **487-230**



Product Details

RS Pro combination pliers are made from chrome vanadium steel and have a overall length of 150 m. They have dual component non-slip handle with finger guard and a jaw length of 34 mm. The combination pliers meet BS3087 standards.

Features and Benefits

- Dual component non-slip handle with finger guard
- Made from drop forged steel with bright natural finish
- Combination pliers made from Chrome Vanadium Steel



ENGLISH

Specifications:

Cutting Capacity Screws	M3.5
Cutting Capacity Standard Wire	1 mm
Cutting Capacity	1 mm
Jaw Length	34 mm
Material	Chrome Vanadium Steel
Maximum Capacity	1 mm
Overall Length	150 mm

COMBINATION PLIER

Material: Chrome Vanadium Steel for Pliers, P.P / TPR Double Injection Handles

Finish: Fully Polish Finish for Pliers, Red Color (P.P) / Black TPR Injection Handle.

Hardness: Heat Treated to HRC: 55° ~ 65° (Cutting Edge), HRC: 40° ~ 50° (Handle) and HRC: 30° ~ 50° (Joint)

RS No.	Description	Handle Overall length	Jaw length	Joint thickness	Joint width	Nose thickness	handle color
487-230	150 mm(6")	158mm	34mm	8.5mm	23mm	4mm	Red P.P/ Black TPR double injection
487-236	180 mm(7")	182mm	37mm	10mm	25mm	4mm	Red P.P/ Black TPR double injector
487-246	200 mm(8")	195mm	39mm	10mm	27mm	4mm	Red P.P/ Black TPR double injection

Remarks:

Handle Spin, Clearance test of Jaw, Cutting Tests, Permanent and Humidity Meet DIN-ISO Standard.