

RECHARGEABLE SPOT LAMP

779.EYEPB

- Power Settings: **Low / Medium / High**
- Lumens: **500 / 1000 / 1500**
- Base with powerful **magnets** for hands-free use
- **180°** Rotation
- Run-time: **7.0** hours on Low mode
- Cordless & Rechargeable, Corded
- IP Rating: **IP67**
- IK Rating: **IK07**
- **UNIQUE DESIGN**
- CRI: **85** keep a natural color
- Optional Tri-Pod Stand (code: 779.TRIPODPB)



180° rotation

Magnetic base

- Dimensions (L x H x w) : 175 X 80 X 125 mm
- Weight : 0,760 KG

