



DESCRIPTION CONTROL			
REV	DESC	DATE	ECN NO




*	390	CARTON:46*30*25CM	A/R	PCS
*	390	PE BAG:30*28*0.08MM	A/R	PCS
*	390	PE BAG:8*10*0.06MM	1	PCS
14		CORE:17.5*27*9.5MM	2	PCS
13		SRW-RE32/BK10	4	PCS
12		HI TEAMP TAPE:W:25MM;L:80MM	2	PCS
11		FOIL-CU-30*65MM	2	PCS
10		PVC-BK10/50	56.6	G
9		SOL-WIRE-FLL-TIN-1.2	3.0	G
8		PE-5321	13	G
7		SOL-WIRE-FULL-TIN-1.0	1.2	G
6		TUBE-HT-Ø3.0*10MM (薄型)	8	PCS
5		TUBE-HT-Ø2.0*6MM (薄型)	14	PCS
4		TUBE-HT-Ø1.0*15MM (薄型)	8	PCS
3		TUBE-HT-Ø1.0*5MM (薄型)	6	PCS
2		D.V.I-24+KEY-M(BLACK)(Nickel Plated Shell) (PIN GOLD FLASH)	2	PCS
1	100204919R09	28-[(1P+D+A+MY)*7C+1P+3C] +MYLAR+A+D+B-BLACK10-8.6U20276 (COPARTNER OR EQUIV)	5.0	M
NO	PART NO.	DESCRIPTION	QTY	UNIT



RoHS COMPLIANT



OUTER MOLDING	AV-DVI053	HT006		
INNER MOLDING	AV-DVI052			
		ITEM: 489371		REV R
DRAW, BY: 鍾有涓		SCALE: NONE	DATE: 2007-12-02	
CHECK, BY:		CUSTOMER: C331<RS>	PAGE: 1/1	
APP, BY:		CUSTOMER P/N:		
ALL DIMENSIONS IN mm				