


Tooling NO.

MD9M TOOLING:K990407

REVISIONS

DATE	LTR	DESCRIPTION	APVD



PIN ASSIGNMENT:

MD9 M	1	2	3	4	5	6	7	8	9	SHELL
	Black	White	Red	Yellow	Purple	Blue	Green	Brown	Gray	Drain
	NC	NC	NC	NC	NC	NC	NC	NC	NC	NC

Specifications:

Temperature Range: -25°C To +85°C
 Current Rating: 1A AC/DC
 Insulation Resistance: 50MΩ Min.
 Voltage Rating: 50V AC/DC
 Withstanding Voltage: 500V AC For 1 Min.



UNLESS OTHERWISE SPECIFIED TOLERANCE: X ±0.2 ANGLES: ±2° X.X ±0.1 X.XX ±0.05 DO NOT SCALE DRAWING		TITLE Plug To Free End MiniDin Cable Assemblies	
DRAWN BY LINJEA	SIZE UNIT MM	PART NO. 232-8906	
CHECKED BY <i>[Signature]</i>	SCALE 1 : 1	THIRD ANGLE PROJECTION 	PAGE 1 OF 1
APPROVED BY <i>[Signature]</i>	DWG NO. DEWP2001062710X0	ITEM NO. CM09M28090066NM-01E	DATE 06/27/2001

ITEM	QTY	U/M	PART NO.	DESCRIPTION
3	2.09	M1	CABLE	Non-UL 28AWG 9C.+Drain+AL/Fail, Jacket Color: Black.
2		KG	1-1487209-3	Molded PVC Color: Black.
1	1	EA	1-1487179-7	MD9 Male, Contact: Gold Flash, Shell: Nickel Plated, Insulation: Black.