

## Datasheet

# RS Pro Mechanical HVAC Thermostat, RS Pro RTRE3521, NC 16 A, 4 A

RS Stock No: **375-0130**



## Product Details

RS Pro NC HVAC thermostat has a front mounted, graduated temperature adjustment dial. This tamperproof thermostat has a plain front cover concealing the temperature adjustment control and a temperature set-back of approximately 6°C. It has a contact rating of 16 A, 4 A and voltage rating of 230 V ac.

## Features and Benefits

- Surface mounting with a thermoplastic front cover
- Fitted with a shunt accelerator heater to ensure low switching differential and to avoid overshoot
- Suitable for industrial and commercial applications



**Specifications:**

Contact Rating	16 A, 4 A
Maximum Temperature	+30°C
Minimum Temperature	+5°C
Supply Voltage	230 V ac
Switch Configuration	NC
Temperature Range	+5 to +30°C