

Datasheet

RS Pro TH110 Nylon Terminal Block Housing IP44, Cable Mount

RS Stock No: **456-1060**



Product Details

RS Pro inline terminal block housing has nylon construction with IP44 rated protection for added security. It comes with integral strain relief clamps and rubber grommets. This terminal block has 3 contacts that is current rated for 17.5 A and voltage rated for 450 V.

Features and Benefits

- Nylon construction
- IP44 rated
- Integral strain relief clamps and rubber grommets
- 3 number of contacts
- Current rated for 17.5 A
- Voltage rated for 450 V



Specifications:

IP Rating	IP44
Material	Nylon
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-20°C
Mounting Type	Cable Mount
Number of Contacts	3