

Datasheet

Cable Stripper 0.05 to 0.5mm Square Use With Solid Wire

RS Stock number [540-1509](#)



Specification:

- Material: High carbon steel sheet (sk-5) for body of crimping tools, low carbon steel (s1018c) for lock screws & rivet, medium carbon steel (ss41) for lock lid, PVC grip and spring steel for high tension return spring
- Finish: Grounding cut edges, chemical black finish and red colour vinyl grip
- Hardness: Heat treated to HRC: 49 ~ 50.5 (whole body) and HRC: 30 ~ 40 (screws)

Contents:

1 pc-6-1/4" (155mm) serrated tip solid wire stripper pliers with lock lid, automatic return spring and red colour vinyl grip - it fit to AWG 10~20 gauges wire, range for diameter of wire are 0.80 ~ 2.60 mm (thickness of blade - 3.2 mm and net weight - 125 grams)