



ENGLISH

Datasheet

## RS Pro M3 to M12 Die Set

RS Stock No: **668-0775**



### Product Details

RS Pro M3 to M12 metric die set contains M3, M4, M5, M6, M8, M10 and M12 dies with diecast die holder. This dies are made of high quality HS steel of ISO standards.

### Features and Benefits

- High quality
- High speed steel
- M3, M4, M5, M6, M8, M10 and M12 dies
- Diecast die holder
- ISO standard



ENGLISH

### Specifications:

Kit Contents	7 x DIN223 25x9 Round Dies, DIN225 25x9 Die Holder
Kit Type	Die Set
Largest Thread Size	M12
Smallest Thread Size	M3
Thread Size Range	M3 to M12

**HSS Circular Dies, BS1127, Left hand thread, with split**

RS STOCK NUMBER		Size(mm)	Outside Diameter	Thickness (mm)
6680744		M3X0.5	13/16"(20.63mm)	6.35
6680753		M4x0.7	13/16"(20.63mm)	6.35
6680756		M5x0.8	13/16"(20.63mm)	6.35
6680750		M6x1.0	13/16"(20.63mm)	6.35
6680769		M8x1.25	1 5/16"(33.33mm)	11.11
6680762		M10x1.5	1 5/16"(33.33mm)	11.11
6680766		M12x1.75	1 5/16"(33.33mm)	11.11

**HSS Circular Dies, DIN223, without split**

RS STOCK NUMBER		Size(mm)	Outside Diameter(mm)	Thickness (mm)
6680716		M3X0.5	25	9
6680725		M4x0.7	25	9
6680728		M5x0.8	25	9
6608722		M6x1.0	25	9
6680731		M8x1.25	25	9
6680734		M10x1.5	25	9
6680738		M12x1.75	25	9
6680740		3/8-24UNF	25.4	9
6680747		1/4-28UNF	25.4	9
6680775		M3-M12	25	9