

Datasheet

HSS 63 mm 90° Countersink, 16.5mm Head Diameter, 3 Flutes

RS Stock number 673-8717



90deg 3 flute countersinks, round shank

Dimensions:

NOMINAL HEAD DIA.	OVERALL LENGTH	SHANK LENGTH	SHANK DIA.	POINT ANGLE	NO. OF FLUTE
6.3mm	45mm	35mm	5mm	90°	3
8.3mm	50mm	38mm	6mm	90°	3
10.4mm	50mm	36mm	6mm	90°	3
12.4mm	56mm	41mm	8mm	90°	3
16.5mm	60mm	42mm	10mm	90°	3
20.5mm	63mm	42mm	10mm	90°	3
6.3,8.3,10.4,12.4,16.5,20.5mm in metal box					3