



ENGLISH

Datasheet

Straight Die Grinders

6mm Air Powered Die Grinder

[RS Stock No. 739-8391](#)



Specifications:

Type of tool	: 6mm Die Grinder
Power Source	: Compressed air
Maximum permissible operating pressure	: 90 psi (6.2 bar)
Recommended operating pressure	: 90 psi (6.2 bar)
Material	: Aluminium
Size	: 6mm Collet
Free Speed	: 22,000RPM
Weight	: 0.6kgs / 1.37lbs
Length	: 6.9" / 175mm
Min Hose Size	: 10mm
Air inlet thread	: 1/4"
Sound	: 93dBA
Vibration	: 5.4m/s ²
Ave Air Consumption	: 3cfm / 85 l/min
Recommended lubrications	: 10 Weight SAE Oil

Features:

- Medium motor size
- 6mm collet (3 piece design)
- Rear exhaust through handle
- High velocity, low vibration
- Safety throttle lever
- Positive throttle action
- Very versatile, excellent in confined workspace

Declaration of Conformity

We RS Components Ltd, declare under our sole 739-8398– Die Grinder responsibility that the conforms with the directive 2006/42/EEC and the standards EN 792-6 ISO 28927.