



739-8430 Data Sheet

ENGLISH

RS stock number : 739-8430
Type of tool : Mini 2" Sander
Weight of tool : 0.34 kg

Power Source : Compressed air
Maximum permissible operating pressure : 90 psi (6.2 bar)
Recommended operating pressure : 90 psi (6.2 bar)
Key Product Benefits

739-8430

Mini 2" Sander

Technical Data

Features

Small sanding pad allows the operator to reach small areas
Random orbit allows maximum operator control and finish
Rear exhaust to keep airflow away from the hand
High power motor designed for efficient sanding

Specifications

Dia Orbit: 3mm
Pad Size: 2" / 50mm
Weight: 0.34kgs / 0.75lbs
Length: 4.92" / 125mm
Vibration: 3.8m/s²
Sound: 81dBA
Free Speed: 16,500RPM
Min Hose Size: 3/16"
Air inlet thread: Rp 1/4
Ave Air Consumption: 1.83cfm / 51.8 l/min
Recommended lubrications: 10 Weight SAE Oil



Declaration of Conformity

We	RS Components Ltd
declare under our sole responsibility that the	739-8430 – Mini 2" Sander
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927