



# 739-8446 Data Sheet

ENGLISH

RS stock number : 739-8446  
Type of tool : Mini 10mm Air Drill  
Weight of tool : 0.43 kg

## 739-8446

Power source : Compressed air  
Maximum permissible operating pressure : 90 psi ( 6.2 bar )  
Recommended operating pressure : 90 psi ( 6.2 bar )

### Mini 10mm Air Drill

#### **Features**

Palm size Drill allows the operator to reach small areas  
Compact and lightweight design allows maximum operator control and performance  
Rear exhaust to keep airflow away from work area  
High power motor for consistent performance

#### **Technical Data**

#### **Specifications**

Size: 10mm / 3/8" Chuck  
Free Speed: 6,000RPM  
Weight: 0.43kgs / 0.95lbs  
Length: 4.72" / 120mm  
Min Hose Size: 3/16"  
Air Inlet thread: Rp 1/4  
Sound: 81dBA  
Vibration: 4m/s<sup>2</sup>  
Ave Air Consumption: 1.68cfm / 48 l/min  
Recommended lubrications: 10 Weight SAE Oil



#### **Declaration of Conformity**

We	RS Components Ltd
declare under our sole responsibility that the	739-8446 – Mini 10mm (3/8") Air Drill
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927