



ENGLISH

Datasheet

RS Pro Non-Fused Terminal Block, 12 Way/Pole, Screw Down Terminals, 2.5 mm² Through Hole, Nylon, 400 V

RS Stock No: **464-9738**



Product Details

RS Pro non-fused terminal block in natural colour, has 12-way terminal blocks with wire protection leaf. This block with 2.5-mm² wire, features screw down termination. The terminal block made of nylon, has 400 V voltage rating.

Features and Benefits

- Brass contacts
- Nickel plated contacts
- 24 A current rating
- 10 mm pitch

**Specifications:**

Contact Material	Brass
Contact Plating	Nickel
Current Rating	24 A
Material	Nylon 66
Maximum Operating Temperature	+125°C
Mounting Type	Through Hole
Number of Ways	12
Pitch	10 mm
Termination Method	Screw Down
Voltage Rating	400 V
Wire Size	2.5 mm ²
Colour	Natural
Screw Size	M3 x 6
Standards Met	RoHS, CE, UL 94V-2, IEC 695-2-1, 2