

Datasheet

RS Pro AC Analogue Panel Voltmeter, 500V, 68 x 68 mm,

RS Stock No: **901-0520**



Product Details

RS Pro analogue panel voltmeter has cut-out dimensions of 68 x 68 mm, is a moving iron for 500 V ac current. It has ABS and polycarbonate enclosure. The operating temperature ranges from -25 to +50°C.

Features and Benefits

- Panel mounting
- Case and terminal protection material UL 94V0
- 1.5 accuracy class

**Specifications:**

Approvals	RoHS Compliant; CE; TUV; UL E327849
Current Type	AC
Meter Type	Moving Iron
Cutout Height	68 mm
Cutout Width	68 mm
Depth	36.5 mm
Maximum Displayed Value	500 V
Maximum Temperature	+50°C
Measurement Range	0 to 500 V
Minimum Displayed Value	0 V
Minimum Temperature	-25°C
Cutout Size	68 x 68 mm
Meter Accuracy	±1.5%
Dimensions	72 x 72 mm
Enclosure Material	ABS, PC
Mounting Type	Panel Mount