

Datasheet

**RS Pro AC Analogue Panel Voltmeter, 68 x 68 mm,**

RS Stock No: **901-0573**



## Product Details

RS Pro analogue panel voltmeter has cut-out dimensions of 68 x 68 mm, is a moving iron for AC current. It has ABS and polycarbonate enclosure. The operating temperature ranges from -25 to +50°C.

## Features and Benefits

- Panel mounting
- Case and terminal protection material UL 94V0
- 1.5 accuracy class

**Specifications:**

Approvals	RoHS Compliant; CE; TUV; UL E327849
Current Type	AC
Meter Type	Moving Iron
Cutout Height	68 mm
Cutout Width	68 mm
Depth	36.5 mm
Maximum Displayed Value	65 Hz
Maximum Temperature	+50°C
Measurement Range	45 to 65 Hz
Minimum Displayed Value	45 Hz
Minimum Temperature	-25°C
Cutout Size	68 x 68 mm
Meter Accuracy	±1.5%
Dimensions	72 x 72 mm
Enclosure Material	ABS, PC
Mounting Type	Panel Mount