



ENGLISH

Datasheet

## RS Pro 12mm Hose Reel 20, Wall Mounting

RS Stock No: **911-9453**



### Product Details

RS Pro wall mounting hose reel has an inner diameter of 12 mm. This stainless steel wash down hose reel with a 20 m braiding is suitable for hot water up to a maximum pressure of 400 bar. It has conventional spring return mechanism.

### Features and Benefits

- Up to 150° working temperature
- 1/2 Inch inlet connection size
- Manufactured from 304 stainless steel
- Viton seals
- Automatic retraction operation
- BSPT inlet thread standard



**Specifications:**

Hose Included	Yes
Inlet Connection	1/2 in Male
Inlet Thread Standard	Metric
Mounting	Wall Mount
Retraction Operation	Automatic
Hose Inner Diameter	12 mm
Inlet Connection Size	1/2 in
Maximum Working Pressure	20 bar