



ENGLISH

Datasheet

RS Pro Steel Hex Bolt, M10 x 150mm

RS Stock No: **917-3182**



Product Details

RS Pro hex bolt is of size M10 x 150 mm, features bright zinc plated steel construction for durability. This high tensile steel hex bolt is partially threaded and can be used with a nut or in a tapped hole. This bolt is tightened with a wrench. The metric threaded hex bolt meets DIN 931 standards.

Features and Benefits

- Good corrosion resistance
- Recyclable
- Non-magnetic
- It is suitable for machine repairs and outdoor applications
- Threaded in accordance with DIN 931



ENGLISH

Specifications:

Finish	Bright Zinc Plated
Material	Steel
Steel Type	High Tensile Steel
Grade	8.8
Length	150 mm
Thread Pitch	1.5
Thread Size	M10
Head Height	6.4 mm
Specification	DIN 931
Width Across Corners	18.9 mm
Width Across Flats	17 mm