

Datasheet

RS 12 Core Screened Industrial Cable, PVC Sheath, 6.9mm OD, 0.22 mm² CSA 1 A, 300 V, 100m

Stock Number - 660-0463



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):300

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor:Tinned Copper

Conductor Dia. (mm): 0.20±0.008 x 7

Insulation: PVC

Insulation Dia. (mm): 1.2±0.05 x 12C

Tape: Mylar Spiral

Coverage:≥115%

Braid Shield : Tinned Copper

Conductor Dia. (mm): 0.15

Conductor Qty: 16x8

Pitch(mm):

Coverage : 91%

ID Thread : Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 6.9±0.2

Colour:

**The colour of the insulation: Red , Blue , Green ,
Yellow ,**

**White , Black , Brown , Violet , Orange , Pink , Light
Green ,**

Grey

The jacket colour: Black

Marking(3times/m):

RS 6600463 7 - 2 - 12C

Electrical Characteristics:

Max.Conductor DC Resistance at 20°C (Ω /Km) :

<86.2

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :

>200

Current Rating : 1 A

