



ENGLISH

Datasheet

RS 6 Core Unscreened Industrial Cable, PVC Sheath, 4.8mm OD, 0.22 mm² CSA 1 A, 440 V, 100m

Stock Number - 660-4043



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):440

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor:Tinned Copper

Conductor Dia. (mm): 0.20±0.008 x 7

Insulation: PVC

Insulation Dia. (mm): 1.2±0.05 x 6C

Fiiler: 1.2 PVC Strip

Tape: Mylar Spiral

Coverage:≥115%

ID Thread : Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 4.6±0.1

Colour:

The colour of the insulation: Red ,

Blue , Green , Yellow ,

White , Black

The jacket colour: Black

Marking(3times/m):

RS 6604043 7 - 2 - 6A

Performance:

Electrical Characteristics:

Max.Conductor DC Resistance at 20°C (Ω /Km) :

<92

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :

>200

Current Rating : 1 A

