

Datasheet

## RS Pro Bright Zinc Plated Steel Insert, M4, 11.89mm

RS Stock No: **768-0723**



### Product Details

Rs Pro threaded hollow cavity insert has bright zinc plated stainless steel construction for added durability. This cavity insert is suitable for use in thin, soft or brittle materials and are self adjusting to cope with a wide range of material thickness. The insert is supplied with friction wrench to aid installation using ordinary screws. This insert can be use with plasterboard, plastic, steel and with aluminium sheets. The body measures 21.36 mm deep with a body outside diameter of 8.08 mm and a fixing hole diameter of 8.38 mm. It has M4 threads for easy installation.

### Features and Benefits

- Suitable for plasterboard, plastic, steel and aluminium sheet
- Supplied with friction wrench to aid installation using ordinary screws
- Made from bright zinc plated mild steel

**Specifications:**

Body Depth	21.36 mm
Body Outside Diameter	8.08 mm
Finish	Bright Zinc Plated
Fixing Hole Diameter	8.38 mm
Flange Diameter	11.89 mm
Material	Steel
Thickness of Material Maximum	9.53 mm
Thickness of Material Minimum	4.75 mm
Thread Size	M4