

Datasheet

## RS Pro Bright Zinc Plated Steel Insert, M6, 15.88mm

RS Stock No: **768-0748**



### Product Details

Rs Pro threaded hollow cavity insert has bright zinc plated stainless steel construction for added durability. This cavity insert is suitable for use in thin, soft or brittle materials and are self adjusting to cope with a wide range of material thickness. The insert is supplied with friction wrench to aid installation using ordinary screws. This insert can be use with plasterboard, plastic, steel and with aluminium sheets. The body measures 23.34 mm deep with a body outside diameter of 11.13 mm and a fixing hole diameter of 11.43 mm. It has M6 threads for easy installation.

### Features and Benefits

- Suitable for plasterboard, plastic, steel and aluminium sheet
- Supplied with friction wrench to aid installation using ordinary screws
- Made from bright zinc plated mild steel

**Specifications:**

Body Depth	23.34 mm
Body Outside Diameter	11.13 mm
Finish	Bright Zinc Plated
Fixing Hole Diameter	11.43 mm
Flange Diameter	15.88 mm
Material	Steel
Thickness of Material Maximum	9.53 mm
Thickness of Material Minimum	4.75 mm
Thread Size	M6