

Datasheet

DIN Connector Sockets, ME - 209/S

RS Stock number 811-8266



Specifications:

Connection Type:	2 Pole + Earth
Voltage:	250V AC
Approvals:	N.A
Standard:	N.A.
Mounting:	Screw-type
Type:	ME-Socket - Non-illuminated
Socket Type:	Type A
Mounting:	M3 Screw
Material For Rubber Gasket:	Nitril / Silicon
Material Body:	Nylon-6 GF
Gland Size:	PG-9
Body Colours:	Black, Grey
Contact Resistance (Initial):	20 m Ohms max.
Current Carrying Parts:	Copper Alloy, Tin plated
Permissible Temp. With/Without Load:	0°C to 90°C
Rating:	10A, 250VAC
Terminals:	Screw-type
H. V. Breakdown Test:	2KV AC For 1 Minute .
Insulation Resistance:	100 M Ohms min.

Unit mm

