

Datasheet

RS Pro Non-Fused Terminal Block, 10 Way/Pole, Screw Terminals, 2.5 mm², PC, 450 V

RS Stock No: **868-0733**



Product Details

RS Pro non-fused terminal block is designed for termination or the joining of cable ends. This 10-way polycarbonate terminal block with 2.5-mm² wire, features screw termination. The panel mount terminal block with brass contact, has a voltage rating of 450 V. This terminal block meets EN 60998-1: 2004 and EN 60998-2-1: 2004 standards.

Features and Benefits

- Transparent blue polycarbonate housing UL 94 - V0
- Funnel cable entry
- Screw clamp
- Peak operational temperature of 85°C
- Brass clamp
- Screw material: galvanised steel
- High mechanical resistance with good electrical characteristics

**Specifications:**

Contact Material	Brass
Enclosed	Yes
Material	PC Housing
Maximum Operating Temperature	+85°C
Mounting Type	Panel Mount
Number of Ways	10
Termination Method	Screw
Voltage Rating	450 V
Wire Size	2.5 mm ²
Colour	Transparent Blue
Standards Met	RoHS, UL 94V-0, EN 60998-1:2004, EN 60998-2-1:2004