




ECN MARK	ECN NO.	DESCRIPTION	DATE



### 7P+5C(30AWG)

(1/0.23BC\*1P+1/0.23BC+AL+MY)\*7P+  
 1/0.23BC\*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG  
 PVC Jacket



### 7P+5C(

28+30# ODI  
 (1/0.32BC\*1P+1/0.23BC+AL+MY)\*7P+  
 1/0.23BC\*5C+AL/MY+1/0.23BC+16/8/0.12#ALMG  
 PVC Jacket

LENGTH	AWG
10000mm	28AWG OD:8.6
7500mm	28AWG OD:8.6
5000mm	30AWG OD:7.3
3000mm	30AWG OD:7.3
2000mm	30AWG OD:7.3
1000mm	30AWG OD:7.3

5		PVC BLACK	2PC	
4		Cover	4PC	
3		DM Male 24*1PIN Gold plated	1PC	
2		DM Male 24*1PIN Gold plated	1PC	
1		PVC BLACK	1PC	
NO.	DWG NO	DESCRIPTION&SPECIFICATION	QTY.	REMARK

TOLERANCE	SIGNATURES	DATE
30-49 ±0.00 100-499 ±0.00 1000-9999 ±0.00 10000-9999 ±0.00	DRAFT: Jay CHECKED: Neo APPROVAL: James	
Unit:MM		REV

CPDVI002		
SCALE	TITLE	DWG NO
A1		

